



# MAGNUM VENUS PRODUCTS

CATALYST MANIFOLD FOR INNOVATOR PLUS	CM-10000
--------------------------------------	----------

Parts List			
ITEM	PART NUMBER	QTY	DESCRIPTION
1	CM-1061-SS	1	MANIFOLD BLOCK
2	O-S-013	9	O-RING
3	CM-1056	1	FITTING
4	CM-1053	4	PLUG FITTING
5	CM-1055	1	FITTING
6	CM-1052	1	JIC FITTING
7	RV-1000-1500	1	CATALYST RELIEF VALVE
8	CM-1005	1	SS BALL VALVE
9	CSC-2000-M	1	CAT ACCUMULATOR ASSY
10	CG-2000	1	Ø2" GAUGE 0-2000 PSI
11	F-LN-04C	2	LOCK NUT
12	MS-2052-30	2	CLEAR POLY TUBE - 1/4"x 30"
13	CPRV-1002-A	1	CPRV HOSE FITTING
14	0116CS	1	FLOW SENSOR BODY
15	0118CS	1	END CAP
16	0946	1	SPRING
17	CTS-9003-01	1	FLOW MAGNET (STANDARD)
18	O-S-015	1	O-RING
19	PF-HN-02-SS	1	HEX NIPPLE
20	VHPC-1003	1	INLET TUBE FITTING
21	PF-HN-02-03J-SS	1	HEX NIPPLE
22	PF-ME-02-03J-SS	1	MALE ELBOW
24	F-HB-04C-32	2	HEX BOLT

**SENSOR ADJUSTMENT:**

MOVE SENSOR HOUSING ALL THE WAY TO THE BOTTOM OF THE FLOW TUBE.  
IF THE SENSOR LIGHT IS NOT ILLUMINATED, MOVE THE SENSOR HOUSING UP  
UNTIL ILLUMINATED.

SENSOR WILL SENSE THE BOTTOM OF THE MAGNET. WHEN THE MAGNET MOVES  
OUT OF THE SENSOR RANGE DUE TO FLUID FLOWING IT WILL TURN THE SENSOR  
OFF.

# MAGNUM VENUS PRODUCTS